

Product datasheet

Specifications



APC 17" Rack LCD Console - United Kingdom

AP5717UK

Overview

Lead time Usually in Stock

Main

Main Input Voltage	100 V 240 V
Number of rack unit	1U
Provided equipment	C13-C14 power cord Documentation CD Firmware upgrade cable Installation guide NEMA 5-15 power cord PS2 KVM cable Single user rack mount kit USB cable USB KVM cable

Physical

Colour	Black
Height	4.4 cm
Width	48.2 cm
Depth	61.4 cm
Net weight	15.9 kg
Mounting location	Front Rear
Mounting preference	No preference
Mounting mode	Not rack-mountable
Maximum mounting depth	104.98 cm
Minimum mounting depth	68 cm

Input

Network frequency 50/60 Hz

Conformance

Product certifications	C-Tick GOST Industry Canada NOM UL listed
------------------------	---

Standards	EN 55022 class A EN 55024 EN 60950 FCC part 15 class A IEC 60950
------------------	--

Environmental

Ambient air temperature for operation	0...40 °C
--	-----------

Supported Hardware

Display colour	16 colours
Display size	17 inch
Trackball type	PS/2 touchpad USB mouse
Display type	LCD display
Display power consumption	19 W
Pixel size	0.26

Packing Units

Package 1 Weight	19.46 kg
Package 1 Height	15.2 cm
Package 1 width	67.3 cm
Package 1 Length	82.6 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------