

# Product datasheet

Specifications



## 17" Rack LCD Console with Integrated 8 Port Analog KVM Switch

AP5808

### Overview

<b>Presentation</b>	The Rack LCD Console with Integrated KVM Switch combines the functionality of Rack LCD Console and Analog KVM switches in one convenient package optimizing U space in the rack environment, eliminating cable clutter, and offering a value of two products functionality in one package. Keyboard is a US English keyboard layout.
<b>Lead time</b>	Usually in Stock

### Main

<b>Main Input Voltage</b>	120 V 240 V
<b>Input Connection Type</b>	IEC 60320 C14
<b>Number of rack unit</b>	1U
<b>Cable length</b>	1.83 m
<b>Number of cables</b>	1
<b>Provided equipment</b>	USB KVM cable Single user rack mount kit PS2 KVM cable NEMA 5-15 power cord Installation guide Firmware upgrade cable Documentation CD C13-C14 power cord

### Physical

<b>Colour</b>	Black
<b>Height</b>	4.3 cm
<b>Width</b>	48.3 cm
<b>Depth</b>	71.1 cm
<b>Net weight</b>	13.77 kg
<b>Mounting location</b>	Front
<b>Mounting preference</b>	No preference
<b>Mounting mode</b>	Rack-mounted
<b>Maximum mounting depth</b>	104.98 cm
<b>Minimum mounting depth</b>	68 cm

### Input

<b>Network frequency</b>	50/60 Hz
--------------------------	----------

## Conformance

Product certifications	cUL listed C-Tick CE Industry Canada KCC UL listed VDE TAA compliance
Standards	EN 60950 FCC part 15 class A IEC 60950

## Environmental

Ambient air temperature for operation	0...40 °C
---------------------------------------	-----------

## Supported Hardware

Display colour	16 colours
Display size	337.9 (H) x 270.3 (V) 17 inch
Trackball type	PS/2 touchpad USB mouse
Display type	LCD display

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13 cm
Package 1 Width	83 cm
Package 1 Length	66.5 cm
Package 1 Weight	19.86 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

## Recommended replacement(s)