

Product datasheet

Specifications



Rack PDU, Switched, 2U, 30A, 208V, (16)C13



AP7911B

Overview

Lead time Usually in Stock

Main

Main Input Voltage	200 V 208 V 230 V
PDU type	Switched
Main Output Voltage	208 V
Input Connection Type	NEMA L6-30P
Number of rack unit	2U
Cable length	3.66 m
Number of cables	1
Provided equipment	Documentation CD Installation guide Rack mounting brackets

Physical

Colour	Black
Height	8.9 cm
Width	44.4 cm
Depth	25.4 cm
Net weight	6.32 kg
Mounting location	Front Rear
Mounting preference	No preference
Mounting mode	Rack-mounted

Input

[In] rated current	24 A
Permissible voltage	200...240 V
Input current limits	30 A
Load capacity	4992 VA

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Network frequency	50/60 Hz
-------------------	----------

Output

Number of power socket outlets	16 IEC 60320 C13
--------------------------------	------------------

Conformance

Product certifications	cUL listed CSA Industry Canada PSE UL listed
------------------------	----------------------------------------------------------

Standards	FCC part 15 class A ICES-003 UL 60950
-----------	---------------------------------------------

Environmental

Ambient air temperature for operation	0...45 °C
---------------------------------------	-----------

Relative humidity	0...95 %
-------------------	----------

Operating altitude	0...10000 ft
--------------------	--------------

Ambient air temperature for storage	-25...65 °C
-------------------------------------	-------------

Storage Relative Humidity	0...95 %
---------------------------	----------

Storage altitude	0.00...15240.00 m
------------------	-------------------

Packing Units

Unit Type of Package 1	Db
------------------------	----

Number of Units in Package 1	1
------------------------------	---

Package 1 Height	14.6 cm
------------------	---------

Package 1 Width	51.4 cm
-----------------	---------

Package 1 Length	51.4 cm
------------------	---------

Package 1 Weight	8.36 kg
------------------	---------

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

REACH Regulation	REACH Declaration
------------------	-----------------------------------

EU RoHS Directive	Compliant EU RoHS Declaration
-------------------	--------------------------------------------------

Mercury free	Yes
--------------	-----

RoHS exemption information	Yes
----------------------------	---------------------

Environmental Disclosure	Product Environmental Profile
--------------------------	-----------------------------------------------

Circularity Profile	End of Life Information
---------------------	-----------------------------------------

Optimized Energy Efficiency	Energy efficient product
-----------------------------	--------------------------

Take-back	Take-back program available
-----------	-----------------------------

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)