

Product datasheet

Specifications



Power Cord Kit (6 ea), Locking, C13 to C14, 0.6m

AP8702S-WW

⚠ To be discontinued

Overview

Presentation This Series of Rack Power Distribution Units (PDU) comes with Locking IEC Receptacles. The output and input connections are C13 to C14. The cord length is 0.6m. Locking IEC system allows the use of optional locking IEC power cords for added power cord security and enhanced reliability. No tools are required to disengage the locking feature and remove the plug from the locking receptacle.

Lead time Usually in Stock

Main

Input Connection Type IEC 60320 C14

Cable length 0.61 m

Number of cables 6

Physical

Colour Black

Height 24 cm

Width 7 cm

Depth 4 cm

Net weight 0.7 kg

Mounting preference No preference

Mounting mode Not rack-mountable

Input

Max line current 10 A

Input current limits 10 A

Output

Max current draw 10 A

Number of power socket outlets 1 IEC 60320 C13

Power cable length 0.61 m

Conformance

Product certifications CCC
PSE

Environmental

Ambient air temperature for operation	0...70 °C
Relative humidity	20...80 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...75 °C
Storage Relative Humidity	20...80 %
Storage altitude	0.00...15240.00 m

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	24 cm
Package 1 Width	4 cm
Package 1 Length	7 cm
Package 1 Weight	0.7 kg
Number of Units in Package 3	540

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)