

Product datasheet

Specifications



Network Management Card for Easy UPS, 1-Phase

AP9544

Overview

Presentation	Allows for secure remote monitoring and control of an individual Easy UPS via a web browser interface.
Lead time	Usually in Stock

Main

Provided equipment	User manual USB cable
---------------------------	--------------------------

Physical

Height	4.4 cm
Width	5.2 cm
Depth	8.0 cm
Net weight	0.05 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable

Conformance

Standards	CISPR 32 EN 55024 EN 61000-4-2 EN 61000-4-3 EN 61000-4-4 EN 61000-4-5 EN 61000-4-6 EN 61000-4-8 EN 61000-6-2 EN/IEC 62040-2
Product certifications	FCC Class A ICES-003 VCCI class A AS/NZS

Environmental

Ambient air temperature for operation	-5...45 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...65 °C

Storage altitude	0.00...15240.00 m
Storage Relative Humidity	0...95 %

Communications & Management

Communication network type	10/100/1000BASE-T
----------------------------	-------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.4 cm
Package 1 Width	5.2 cm
Package 1 Length	8 cm
Package 1 Weight	0.05 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)