

Product datasheet

Specifications



APC Replacement battery cartridge #140

APCRBC140

Overview

Lead time Usually in Stock

Main

Product or component type Replacement battery cartridge

Battery type Lead-acid battery

Provided equipment Battery recycling guide

Physical

Colour Black

Height 12.2 cm

Width 19.7 cm

Depth 59.7 cm

Net weight 34.55 kg

Mounting mode Not rack-mountable

Environmental

Ambient air temperature for operation 0...40 °C

Operating altitude 0...10000 ft

Relative humidity 0...95 % non-condensing

Ambient air temperature for storage -15...45 °C

Storage altitude 0.00...15240.00 m

Storage Relative Humidity 0...95 % Non-condensing

Batteries & Runtime

Number of battery free slots 0

Number of battery filled slots 0

Device mounting Enclosed battery cartridge

Battery voltage 192 V

Additional information Each APCRBC140 consists of 2 battery modules as shown in the product image.

Number of battery replacement quantity 1

Replacement battery

Packing Units

| | |
|-------------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 22.6 cm |
| Package 1 Width | 78.1 cm |
| Package 1 Length | 40.9 cm |
| Package 1 Weight | 37.27 kg |

Offer Sustainability

| | |
|---------------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |
| Take-back | Take-back program available |

Contractual warranty

| | |
|-----------------|---------------------------|
| Warranty | 2 years repair or replace |
|-----------------|---------------------------|

Recommended replacement(s)