Product datasheet

Specifications





APC Replacement Battery Cartridge #165

APCRBC165

Overview

Lead Time

Usually	in	Stock
Usually		SIUCK

Main

Main Input Voltage	12 V DC
Product Or Component Type	Replacement battery cartridge
Battery Type	Lead-acid battery
Provided Equipment	Installation guide

Batteries & Runtime

Number Of Battery Free Slots	0
Number Of Battery Filled Slots	0
Number Of Battery Replacement Quantity	1

Physical

-	
Colour	Black
Height	7.6 cm
Width	15.2 cm
Depth	20.3 cm
Net Weight	5.2 kg
Mounting Mode	Not rack-mountable

Environmental

Ambient Air Temperature For Operation	045 °C
Operating Altitude	010000 ft
Relative Humidity	095 % non-condensing
Ambient Air Temperature For Storage	-545 °C
Storage Altitude	0.0015240.00 m
Storage Relative Humidity	095 % non-condensing

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1



Package 1 Height	14.6 cm
Package 1 Width	27.5 cm
Package 1 Length	23.4 cm
Package 1 Weight	5.53 kg
Scc14	10731304346873

Contractual warranty

Warranty

2 years repair or replace

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.





Transparency RoHS/REACh

Well-being performance

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information



