

# Product datasheet

Specifications



## APC Replacement Battery Cartridge #165

APCRBC165

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage 12 V DC  
Product or component type Replacement battery cartridge  
Battery type Lead-acid battery  
Provided equipment Installation guide

### Physical

Colour Black  
Height 7.6 cm  
Width 15.2 cm  
Depth 20.3 cm  
Net weight 5.2 kg  
Mounting mode Not rack-mountable

### Environmental

Ambient air temperature for operation 0...45 °C  
Operating altitude 0...10000 ft  
Relative humidity 0...95 % non-condensing  
Ambient air temperature for storage -5...45 °C  
Storage altitude 0.00...15240.00 m  
Storage Relative Humidity 0...95 % non-condensing

### Batteries & Runtime

Number of battery free slots 0  
Number of battery filled slots 0  
Number of battery replacement quantity 1

---

Replacement battery

## Packing Units

---

|                              |                |
|------------------------------|----------------|
| Unit Type of Package 1       | Db             |
| Number of Units in Package 1 | 1              |
| Package 1 Height             | 14.6 cm        |
| Package 1 Width              | 27.5 cm        |
| Package 1 Length             | 23.4 cm        |
| Package 1 Weight             | 5.53 kg        |
| SCC14                        | 10731304346873 |

## Offer Sustainability

---

|                   |  |
|-------------------|--|
| EU RoHS Directive | Not applicable, out of EU RoHS legal scope |
|-------------------|--|

## Contractual warranty

---

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|

Recommended replacement(s)