

# Product datasheet

Specifications



## NetShelter 2 Post Rack 45U #12-24 Threaded Holes Black

AR201

### Overview

Lead time Usually in Stock

### Main

|                     |  |
|---------------------|--|
| Number of rack unit | 45U  |
| Number of cables    | 1  |
| Provided equipment  | 24 x #12-24 x 0.5 inch pilot screws<br>User manual |

### Physical

|                            |                    |
|----------------------------|--------------------|
| Colour                     | Black              |
| Height                     | 213.6 cm           |
| Width                      | 51.3 cm            |
| Depth                      | 37.6 cm            |
| Net weight                 | 11.82 kg           |
| Mounting location          | Front              |
| Mounting preference        | No preference      |
| Mounting mode              | Not rack-mountable |
| Maximum mounting depth     | 104.8 cm           |
| Rack width                 | 19"                |
| Marking                    | 3 gauge post       |
| Permanent permissible load | 340.19 kg static   |

### Conformance

|                        |                  |
|------------------------|------------------|
| Product certifications | UL listed<br>TAA |
| Standards              | EIA-310E         |

### Packing Units

|                              |       |
|------------------------------|-------|
| Unit Type of Package 1       | PCE   |
| Number of Units in Package 1 | 1     |
| Package 1 Height             | 10 cm |

|                  |        |
|------------------|--------|
| Package 1 Width  | 220 cm |
| Package 1 Length | 16 cm  |
| Package 1 Weight | 14 kg  |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| Take-back                  | Take-back program available   |

## Contractual warranty

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|

## Recommended replacement(s)