

Product datasheet

Specifications



APC EASY UPS BV 650VA, AVR, Universal Outlet, 230V

BV650I-MSX

Overview

Lead Time Usually in Stock

Main

Main Input Voltage	230 V
Main Output Voltage	230 V
Rated Power In W	375 W
Rated Power In Va	650 VA
Input Connection Type	BS1363A British
Output Connection Type	4 universal receptacle
Cable Length	1.50 m
Number Of Cables	1
Battery Type	Lead-acid battery
Provided Equipment	User manual

Batteries & Runtime

Efficiency	View Efficiency Graph
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Life	3...5 year(s)
Replacement Battery	APCRBCV210
Extended Runtime	0

General

Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No
Ups Size	WS

Physical

Colour	Black
Height	9.25 cm
Width	16.5 cm

Depth	30.5 cm
Net Weight	4.5 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	No

Input

Network Frequency	50/60 Hz +/- 5 Hz auto-sensing
Input Voltage Limits	170...280 V

Output

Maximum Configurable Power In W	375 W
Output Frequency	50/60 Hz +/- 1 Hz unsynchronised
Ups Type	Line interactive
Wave Type	Stepped approximation to a sinewave
Graph Display	1
Maximum Configurable Power In Va	650 VA
Transfer Time	6 ms typical : 10 ms maximum

Conformance

Product Certifications	CE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...90 %
Operating Altitude	0...6667 ft
Ambient Air Temperature For Storage	-20...50 °C
Storage Relative Humidity	0...90 %
Storage Altitude	0.00...15240.00 m
Acoustic Level	40 dBA
Ip Degree Of Protection	IP20

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
-------	--

Surge Protection and Filtering

Surge Energy Rate	156 J
-------------------	-------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	23.7 cm
Package 1 Width	37.3 cm
Package 1 Length	14.3 cm
Package 1 Weight	4.8 kg
Scc14	10731304344077

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)



Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

Energy Efficient Product

Take-Back Program Available

Well-being performance

Mercury Free

Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive [Compliant with Exemptions](#)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)
