



# APC EASY UPS BV 650VA, AVR, Universal Outlet, 230V

BV650I-MSX

#### Overview

Lead Time Usually in Stock

#### Main

Walli	
Main Input Voltage	230 V
Main Output Voltage	230 V
Rated Power In W	375 W
Rated Power In Va	650 VA
Product Or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	BS1363A British
Output Connection Type	4 universal receptacle
Cable Length	1.50 m
Number Of Cables	1
Battery Type	Lead-acid battery
Provided Equipment	User manual

#### **Batteries & Runtime**

Efficiency	View Efficiency Graph ☐
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Life	35 year(s)
Replacement Battery	APCRBCV210 ☐
Extended Runtime	0

#### **General**

Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No
Ups Size	WS

## **Physical**

Colour	Black
Height	9.25 cm

Width	16.5 cm
Depth	30.5 cm
Net Weight	4.5 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	No

## Input

Network Frequency	50/60 Hz +/- 5 Hz auto-sensing
Input Voltage Limits	170280 V

## Output

Maximum Configurable Power In W	375 W
Output Frequency	50/60 Hz +/- 1 Hz unsynchronised
Ups Type	Line interactive
Wave Type	Stepped approximation to a sinewave
Graph Display	1
Maximum Configurable Power In Va	650 VA
Transfer Time	6 ms typical : 10 ms maximum

#### **Conformance**

Product Certifications	CE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

#### **Environmental**

Ambient Air Temperature For Operation	040 °C
Relative Humidity	090 %
Operating Altitude	06667 ft
Ambient Air Temperature For Storage	-2050 °C
Storage Relative Humidity	090 %
Storage Altitude	0.0015240.00 m
Acoustic Level	40 dBA
Ip Degree Of Protection	IP20

# Communications & Management

Alarm Alarm when on battery : distinctive low battery alarm : overload continuous tone

**Surge Protection and Filtering** 

Surge Energy Rate 156 J

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	23.7 cm
Package 1 Width	37.3 cm
Package 1 Length	14.3 cm
Package 1 Weight	4.8 kg
Scc14	10731304344077

## **Contractual warranty**

Warranty 2 years repair or replace



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

Learn more about Green Premium >









Energy Efficient Take-back Transparency RoHS/REACh

#### Resource performance

Energy Efficient Product



### Well-being performance

Mercury Free

Rohs Exemption Information Y

#### **Certifications & Standards**

Reach Regulation

Eu Rohs Directive

Compliant with Exemptions

Environmental Disclosure

Product Environmental Profile

Circularity Profile

End of Life Information