

Product datasheet

Specifications

NetBotz Rack Monitor 570

NBRK0570



⚠ Discontinued on: 21 Apr 2022

⚠ Discontinued

Overview

Presentation	Supports up to 4 external camera pods, 12 sensor pods and up to 78 Universal Sensors.
Lead Time	Usually in Stock

Main

Number Of Rack Unit	1U
Number Of Cables	1
Communication Port Protocol	DHCP DNS HTTP HTTPS SMTP SOCKS TCP/IP
Provided Equipment	Country-specific detachable power cord Documentation CD Installation guide Rack mounting brackets Temperature/humidity sensor USB cable
Product Compatibility	4 - 20 mA sensor Camera pod 120 CCTV adapter pod 120 Rack sensor pod 150 Room sensor pod 155 Sensor pod 120 Pelco IPSD4N-W0 Analog CCTV cameras via USB CCTV adapter pod NetBotz USB camera pod NTSC camera PAL camera Pelco IP110-CHV9 Pelco IP3701H-2

General

Camera Frame Rate	Up to 30 fps
Display Resolution	Up to 1280x1024
Connections Supported	4-20mA sensor inputs 4 Alarm beacon 1 Fluid rope leak sensor 1 Relay outputs 2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Universal Sensor Supported	0-5V Door contact Dry contact Humidity Smoke Fluid spot leak Temperature Vibration
Number Of Universal Sensor Ports	6
Number Of Sensor Pods Supported	12
Number Of Universal Sensors Supported	72
Number Of Supported Camera	4 for networked 4 for USB

Physical

Height	4.3 cm
Width	43.2 cm
Depth	9.3 cm
Net Weight	1.74 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Rack-mounted

Conformance

Standards	FCC part 15 class A ICES-003
Product Certifications	AS/NZS 3548 (C-Tick) class A cUL listed CE GOST IRAM low voltage directive 2006/95/EC NOM UL listed VCCI class A VDE

Environmental

Ambient Air Temperature For Operation	0...45 °C
Operating Altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature For Storage	-15...65 °C
Storage Altitude	0.00...15240.00 m
Storage Relative Humidity	0...95 %

Communications & Management

Communication Network Type	RJ45 10/100 Base-T
----------------------------	--------------------

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Number Of Units In Package 1	1
------------------------------	---

Contractual warranty



Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant with Exemptions
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins