

# Product datasheet

Specifications

## NetBotz Rack Monitor 570

NBRK0570



! Discontinued on: 21 April 2022

! Discontinued

### Overview

<b>Presentation</b>	Supports up to 4 external camera pods, 12 sensor pods and up to 78 Universal Sensors.
<b>Lead time</b>	Usually in Stock

### Main

<b>Number of rack unit</b>	1U
<b>Number of cables</b>	1
<b>Communication port protocol</b>	DHCP DNS HTTP HTTPS SMTP SOCKS TCP/IP
<b>Provided equipment</b>	Country-specific detachable power cord Documentation CD Installation guide Rack mounting brackets Temperature/humidity sensor USB cable
<b>Product compatibility</b>	4 - 20 mA sensor Camera pod 120 CCTV adapter pod 120 Rack sensor pod 150 Room sensor pod 155 Sensor pod 120 Pelco IPSD4N-W0 Analog CCTV cameras via USB CCTV adapter pod NetBotz USB camera pod NTSC camera PAL camera Pelco IP110-CHV9 Pelco IP3701H-2

### General

<b>Camera frame rate</b>	Up to 30 fps
<b>Display resolution</b>	Up to 1280x1024
<b>Connections supported</b>	4-20mA sensor inputs 4 Alarm beacon 1 Fluid rope leak sensor 1 Relay outputs 2
<b>Universal sensor supported</b>	0-5V Door contact Dry contact Humidity Smoke Fluid spot leak

Temperature  
Vibration

Number of universal sensor ports	6
Number of sensor pods supported	12
Number of universal sensors supported	72
Number of supported camera	4 networked 4 USB

## Physical

Height	4.3 cm
Width	43.2 cm
Depth	9.3 cm
Net weight	1.74 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Rack-mounted

## Conformance

Standards	FCC part 15 class A ICES-003
Product certifications	AS/NZS 3548 (C-Tick) class A cUL listed CE GOST IRAM low voltage directive 2006/95/EC NOM UL listed VCCI class A VDE

## Environmental

Ambient air temperature for operation	0...45 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...65 °C
Storage altitude	0.00...15240.00 m
Storage Relative Humidity	0...95 %

## Communications & Management

Communication network type	RJ45 10/100 Base-T
----------------------------	--------------------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

## Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
-------------------	--

---

<b>Mercury free</b>	Yes
---------------------	-----

---

<b>RoHS exemption information</b>	Yes
-----------------------------------	-----

---

<b>WEEE</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
-------------	---

---

### **Contractual warranty**

---

<b>Warranty</b>	2 years repair or replace
-----------------	---------------------------

### **Recommended replacement(s)**