

# Product datasheet

Specifications



## APC Replacement Battery Cartridge #4

RBC4

### Overview

Lead time Usually in Stock

### Main

Number of cables 1

Battery type Lead-acid battery

Provided equipment All required connectors  
Battery recycling guide  
Reusable packaging  
Installation guide

### Physical

Colour Black

Height 9.9 cm

Width 9.4 cm

Depth 15 cm

Net weight 3.68 kg

Mounting mode Not rack-mountable

USB compatible No

### Output

Battery capacity 12 Ah

### Environmental

Ambient air temperature for operation 0...40 °C

Operating altitude 0...10000 ft

Relative humidity 0...95 %

Ambient air temperature for storage -15...45 °C

Storage altitude 0.00...15240.00 m

Storage Relative Humidity 0...95 %

## Batteries & Runtime

---

Number of battery free slots	0
------------------------------	---

---

Number of battery filled slots	0
--------------------------------	---

---

Battery voltage	12 V
-----------------	------

---

Number of battery replacement quantity	1
--	---

---

## Packing Units

---

Package 1 Weight	4 kg
------------------	------

---

Package 1 Height	12.4 cm
------------------	---------

---

Package 1 width	17.5 cm
-----------------	---------

---

Package 1 Length	21.3 cm
------------------	---------

---

Number of Units in Package 3	140
------------------------------	-----

---

## Offer Sustainability

---

Sustainable offer status	Green Premium product
--------------------------	-----------------------

---

REACH Regulation	<a href="#">REACH Declaration</a>
------------------	-----------------------------------

---

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
-------------------	---

---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
--------------------------	---

---

Circularity Profile	<a href="#">End of Life Information</a>
---------------------	---

---

Take-back	Take-back program available
-----------	-----------------------------

---

## Contractual warranty

---

Warranty	2 years repair or replace
----------	---------------------------

---