

# Product datasheet

Specifications



## APC Service Bypass Panel 200/208/230/240V 125A HW Input/ Output

SBP20KP

### Overview

Lead time Usually in Stock

### Main

**Main Input Voltage** 200 V  
208 V  
220 V  
230 V  
240 V  
380 V 3 phases  
400 V 3 phases  
415 V 3 phases

**Main Output Voltage** 200 V  
208 V  
220 V  
230 V  
240 V

**Output connector type** Hard wire 3-wire (H N + E) 1  
Hard wire 3-wire (2P + E) 1

**Number of rack unit** 4U

**Number of cables** 1

**Provided equipment** Installation guide  
Rack mounting brackets  
User manual

### Physical

**Colour** Black

**Height** 17.8 cm

**Width** 43.2 cm

**Depth** 55.4 cm

**Net weight** 19.32 kg

**Mounting location** Front

**Mounting preference** Lower

**Mounting mode** Rack-mounted

### Input

**Network frequency** 50/60 Hz

**Number of input connectors** 1 hard wire 3-wire (H N + E)  
1 hard wire 3-wire (2P + E)  
1 hard wire 5-wire (3P + N + E)

Permissible voltage	200...240 V
Max line current	125 A
Input current limits	125 A
Load capacity	20000 VA
Power factor	0...1

## Output

Max current draw	125 A
Protection type	Circuit breaker
Efficiency	99 %

## Conformance

Product certifications	CSA GOST
------------------------	-------------

## Environmental

Ambient air temperature for operation	-20...50 °C
Relative humidity	0...95 %
Operating altitude	0...15000 ft
Ambient air temperature for storage	-40...65 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m

## Packing Units

Package 1 Weight	31.36 kg
Package 1 Height	30.5 cm
Package 1 width	61 cm
Package 1 Length	84.5 cm

## Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

## Contractual warranty

Warranty	2 years (parts only)
----------	----------------------