


Product datasheet

Specifications



Easy UPS Dry Contact Card/Relay I/O card

VGL9901I

Overview

Presentation	High quality, Double-conversion On-line UPS designed for essential power protection needs even in the most unstable power conditions.
Lead Time	Usually in Stock

Main

Provided Equipment	User manual
--------------------	-------------

Physical

Height	2.6 cm
Width	5.2 cm
Depth	8.4 cm
Net Weight	0.05 kg
Mounting Mode	Not rack-mountable

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Ambient Air Temperature For Storage	-15...45 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.8 cm
Package 1 Width	12.4 cm
Package 1 Length	16.6 cm
Package 1 Weight	0.11 kg

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------



Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)

Well-being performance

	Reach Free Of Svhc	
<hr/>		
	Rohs Exemption Information	Yes
<hr/>		
<hr/>		
Reach Regulation		REACH Declaration
<hr/>		
Eu Rohs Directive		Compliant
		EU RoHS Declaration
<hr/>		
China Rohs Regulation		China RoHS declaration
		Pro-active China RoHS declaration (out of China RoHS legal scope)
<hr/>		