Product datasheet

Specifications



Rack PDU, Metered, Zero U, 10A, 230V, (16) C13

AP7850B

Overview

Lead Time Usually in Stock

Main

Colour	Black	
Pdu Type	Metered	
Cord Length	3.05 m	
Number Of Cables	1	
Provided Equipment	Cord retention bracket(s) Installation guide Rack mounting brackets Toolless mounting kit	

Complementary

Input Voltage	200 V 208 V 230 V	
Height	124.5 cm	
Width	5.6 cm	
Output Voltage	Voltage 230 V	
Depth	4.4 cm	
Net Weight	3.07 kg	
Mounting Location	nting Location Side	
Mounting Preference	ng Preference No preference	
Input Plug Type	Type IEC 60320 C14	
Mounting Mode	Rack-mounted	
Rack Units	0U	
Mounting Position	Position Vertical	
Permissible Voltage	ole Voltage 200250 V	
Max Line Current	Current 10 A	
Load Capacity	y 2300 VA	
Network Frequency	4763 Hz	
Total Number Of Outlets	16 IEC 60320 C13	

Environment



Product Certifications	CE GOST VDE	
Ambient Air Temperature For Operation	-545 °C	
Relative Humidity	595 %	
Operating Altitude	010000 ft	
Ambient Air Temperature For Storage	-2565 °C	
Storage Relative Humidity	595 %	
Storage Altitude	0.0015240.00 m	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	213.4 cm
Package 1 Width	32.3 cm
Package 1 Length	38.7 cm
Package 1 Weight	3.98 kg

Contractual warranty

Warranty 2 years repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Learn more about Green Premium >









Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product

Well-being performance

Ø	Lead Free	
⊘	Mercury Free	
9	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information