# **Product datasheet**

Specification





## APC Rack PDU 9000 Switched, ZeroU, 32A, 230V, (21) C13 & (3) C19

APDU9953

#### **Overview**

Lead Time Usually in Stock

#### Main

Colour	Black
Pdu Type	Switched
Cord Length	3.05 m
Number Of Cables	1
Provided Equipment	Installation guide Rack mounting brackets Safety quide

## Complementary

Input Voltage	200 V
	208 V
	230 V
	200 V
Height	182.9 cm
NAP 111	
Width	5.6 cm
Depth	4.6 cm
Net Weight	7.34 kg
Mounting Location	Side
Mounting Preference	No preference
Input Plug Type	IEC 60309 32 A 2P + E
Mounting Mode	Not rack-mountable
Rack Units	0U
Usb Compatible	No
Mounting Position	Vertical
Communication Port Protocol	SNMP
Communication Fort Frotocor	
	Redfish
Permissible Voltage	220240 V
Max Line Current	32 A
Input Current Limits	32 A
Load Capacity	7400 VA
Network Frequency	50/60 Hz

Total Number Of Outlets	21 IEC 60320 C13 3 IEC 60320 C19
Communication Network Type	10/100/1000BASE-T

### **Environment**

Product Certifications	VDE EAC RCM
Standards	EN 55022 class A EN 55024 EN 61000-3-2 EN 61000-3-3
Ambient Air Temperature For Operation	-560 °C
Relative Humidity	595 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2565 °C
Storage Relative Humidity	595 %
Storage Altitude	0.0015240.00 m

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	204 cm
Package 1 Width	12.4 cm
Package 1 Length	16.5 cm
Package 1 Weight	9.95 kg

## **Contractual warranty**

Warranty 3 years repair or replace



**Green Premium**<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Learn more about Green Premium >





Transparency RoHS/REACh

### Well-being performance



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information