

# Product datasheet

Specifications



## APC Easy UPS BVX 1200VA, 230V, AVR, India Sockets

BVX1200LI-IN

### Overview

Lead time	Usually in Stock
-----------	------------------

### Main

Input voltage	230 V
Output voltage	230 V
Output voltage	230 V
Rated power in W	650 W
Rated power in VA	1200 VA
Nb of power socket outlets	6 India 2/3-pin 6A
Cable length	1.22 m
Number of cables	1
Battery type	Lead-acid battery
Provided equipment	User manual

### General

Number of power module free slots	0
Number of power module filled slots	0
Redundant	No
UPS size	WS

### Physical

Colour	Black
Height	19.0 cm
Width	14.0 cm
Depth	39.0 cm
Net weight	7.5 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0

---

USB compatible	No
----------------	----

---

## Input

---

Network frequency	40...70 Hz +/- 5 Hz auto-sensing
Plug standard	India 3-pin 6A
Input voltage limits	140...300 V
Input protection type	Circuit breaker

---

## Output

---

Maximum configurable power in W	650 W
Output frequency	50/60 Hz +/- 1 Hz unsynchronised
UPS type	Line interactive
Wave type	Stepped approximation to a sine wave
Graph display	1
Maximum configurable power in VA	1200 VA
Transfer time	6 ms typical : 10 ms maximum

---

## Conformance

---

Product certifications	BIS
------------------------	-----

---

## Environmental

---

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3000 m
Ambient air temperature for storage	-20...50 °C
Storage Relative Humidity	0...95 % Non-condensing
Storage altitude	0...15000 m
Acoustic level	40 dBA
IP degree of protection	IP20

---

## Batteries & Runtime

---

Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	6 h
Battery voltage	12 V
Battery capacity	9 Ah
Extended runtime	0

---

## Communications & Management

---

Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

---

## Surge Protection and Filtering

---

Surge energy rate 255 J

---

## Packing Units

---

Package 1 Weight 8.5 kg

---

Package 1 Height 29.7 cm

---

Package 1 width 23.5 cm

---

Package 1 Length 49.5 cm

---

## Offer Sustainability

---

REACH Regulation [REACH Declaration](#)

---

EU RoHS Directive Compliant  
[EU RoHS Declaration](#)

---

Mercury free Yes

---

RoHS exemption information [Yes](#)

---

China RoHS Regulation [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information

---

WEEE The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

---

## Contractual warranty

---

Warranty 2 Years on UPS & 1 Year on Battery

---