

Product datasheet

Specifications



APC Smart-UPS RC 1000VA, 230V, no battery, 4x India 3-pin 6A outlets

SRC1KUXI

Overview

Lead time Usually in Stock

Main

Main Input Voltage 230 V

Main Output Voltage 230 V

Other Output Voltage 220 V
240 V

Rated power in W 800 W

Rated power in VA 1000 VA

Plug standard India 3-pin 6A

Output connection type 4 India 3-pin 6A

Cable length 1.52 m

Number of cables 1

Battery type External battery system

Provided equipment Smart UPS signalling RS-232 cable
User manual
Warranty card

General

Number of power module free slots 0

Number of power module filled slots 0

Redundant No

Physical

Colour Black

Height 22 cm

Width 14.5 cm

Depth 40 cm

Net weight 5.7 kg

Mounting preference No preference

Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	No

Input

Network frequency	40...70 Hz India 3-pin 6A
Input voltage limits	110...280 V half load
Switching current capacity	10 A

Output

Maximum configurable power in W	800 W
Harmonic distortion	Less than 2 %
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Crest factor	3 : 1
UPS type	Double conversion online
Wave type	Sine wave
Efficiency	90 % (full load) 88 % (half load)
Maximum configurable power in VA	1000 VA

Conformance

Product certifications	BIS
------------------------	-----

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...3000 ft
Ambient air temperature for storage	-20...60 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...4572.00 m

Batteries & Runtime

Number of battery filled slots	0
Number of battery free slots	0
Battery power in VAH	0 VAh runtime
Extended runtime	0

Communications & Management

Control panel	LED status display with load and battery bar-graphs and on line : on battery : replace battery : and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	34 cm
Package 1 Width	47.8 cm
Package 1 Length	23.5 cm
Package 1 Weight	6.3 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)