

# Product datasheet

Specifications



## APC Smart-UPS RC , 230V, Paralleling kit for 5 and 6KVA

SRCPK0506

⚠ Discontinued on: 26-Sept-2023

⚠ Discontinued

### Overview

Lead Time Usually in Stock

### Main

Main Input Voltage	230 V
Main Output Voltage	230 V
Output Connector Type	Hard wire 3-wire (H N + E) 1
Provided Equipment	Cable ties Parallel communication cable Rack mounting brackets User manual Vertical mounting brackets Warranty card

### Physical

Height	13.2 cm
Width	16.4 cm
Depth	43.2 cm
Net Weight	2.04 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

### Input

Network Frequency	50/60 Hz
Number Of Input Connectors	1 hard wire 3-wire (1P + N + E)
Input Current Limits	70 A
Power Factor	0...1

### Output

Max Current Draw	40 A
Protection Type	Circuit breaker

### Environmental

Ambient Air Temperature For Operation 0...40 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Relative Humidity	0...95 % non-condensing
Operating Altitude	0...3000 ft
Ambient Air Temperature For Storage	-15...65 °C
Storage Relative Humidity	0...95 % non-condensing
Storage Altitude	0.00...4572.00 m

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24.3 cm
Package 1 Width	53.8 cm
Package 1 Length	29.1 cm
Package 1 Weight	7 kg

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

[Learn more about Green Premium >](#)



Energy Efficient   Take-back

## Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

## Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

Reach Regulation   [REACH Declaration](#)

Eu Rohs Directive   Compliant  
[EU RoHS Declaration](#)

China Rohs Regulation   [China RoHS declaration](#)  
Pro-active China RoHS declaration (out of China RoHS legal scope)

Weee   The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins