제품 데이터 시트

110



랙 ATS, 230V, 16A, C20 입력, (8) C13 (1) C19 출력



AP4423

! 판매 중단일 2023. 6. 9.

① 중단

개요

The APC Rack Automatic Transfer Switch (ATS) is a high availability switch that provides redundant power to connected equipment and has two input power cords, one for each AC source. The output configuration is (8) C13 and (1) C19 The Rack ATS supplies power to the connected load from a primary AC source. If that primary source becomes unavailable, the Rack ATS automatically transfers loads to the secondary source. The transfer time from one source to the other is seamless to the connected equipment, as the switching occurs safely between the two input sources regardless of any phase differences. The units have built-in network connectivity, which allows for remote management through Web, SNMP, SHH, Telnet, or StruxureWare™ Data Center Expert. With multiple outlets, several devices can be plugged directly into the Rack ATS without the need for an additional Rack PDU. Current monitoring and alarms help prevent downtime to the equipment by providing aggregate current measurements and warnings when power consumption draws near the maximum rating of the Rack ATS. Built-in network and local interfaces allow

for custom configuration settings for added flexibility.

리드 타임 상시 재고

기본항목

Main Input Voltage	230 V
Main Output Voltage	230 V
Input Connection Type	IEC 60320 C20
Number Of Rack Unit	1U
제공된 장비	장착 하드웨어 랙장착 브라켓 직렬 구성 케이블

물리적 규격

색상	검은색
높이	4.4 cm
너비	43.2 cm
깊이	23.6 cm
제품 무게	3.74 kg
마운팅 위치	전면 후면
Mounting Preference	No preference
마운팅 모드	Rack-mounted

입력

네트워크 주파수 50/60 Hz

Max Line Current	20 A
Input Current Limits	20 A
부하 용량	3700 VA

출력

상(Phase)당 최대 총 전류 소모	16 A
Number Of Power Socket Outlets	8 IEC 60320 C13 1 IEC 60320 C19
 보호 타입	Without circuit breaker

준수 사항

제품 인증	cUL listed CE UL 리스트됨	
표준	EN 55022 클래스 A FCC part 15 class A	

환경 요구 사항

사용온도	-545 °C
상대 습도	595 %
	010000 ft
저장온도	-2565 °C
보관 상대 습도	595 %
스토리지 고도	0.0015240.00 m

포장 단위

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.4 cm
Package 1 Width	35.6 cm
Package 1 Length	60 cm
Package 1 Weight	5.51 kg

계약 보증

보증	2년	

지속 가능성 Sreen Premium™

Green Premium[™] 레이블 은 동급 최고의 환경 성능을 갖춘 제품을 제공한다는 슈나이더 일렉트릭 의 약속입니다. Green Premium은 순환 및 낮은 ${
m CO}_2$ 제품뿐 아니라 최신 규정 준수, 환경적 영향 투 명성 등을 약속합니다.

Green Premium 자세히 알아보기 >







Take-back 투명성 RoHS/REACh

리소스 성능



Take-Back Program Available

웰빙 성과





🕗 수은 없음



☑ Rohs 면제 정보

인증 및 표준

Reach 규정	REACh 선언
Eu Rohs 지침	면제 준수
환경 공시	제품 환경 프로필
순환성 프로필	수명 종료 정보