

Product datasheet

Specifications



Rack ATS, 230 V, 32 A, IEC 309 in, (16) C13 (2) C19 out



AP4424

 To be discontinued on: 1 Nov 2024

 To be discontinued

Overview

Lead Time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	230 V
Main Output Voltage	230 V
Input Connection Type	IEC 60309 32 A 2P + E
Number Of Rack Unit	2U
Cable Length	2.44 m
Number Of Cables	2
Provided Equipment	Rack mounting brackets RS-232 configuration cable Serial configuration cable

Physical

Colour	Black
Height	8.8 cm
Width	43.2 cm
Depth	23.6 cm
Net Weight	6.94 kg
Mounting Location	Front Rear
Mounting Preference	No preference
Mounting Mode	Rack-mounted

Input

Network Frequency	50/60 Hz
Max Line Current	32 A
Input Current Limits	32 A
Load Capacity	7400 VA

Output

Max Current Draw	32 A
------------------	------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Power Socket Outlets	16 IEC 60320 C13
	2 IEC 60320 C19
Protection Type	Circuit breaker

Conformance

Standards	EN 55022 class A FCC part 15 class A
-----------	---

Environmental

Ambient Air Temperature For Operation	-5...45 °C
Relative Humidity	5...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage Altitude	0.00...15240.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21 cm
Package 1 Width	35.6 cm
Package 1 Length	58.4 cm
Package 1 Weight	9.43 kg

Contractual warranty


Warranty	2 years repair or replace
----------	---------------------------


Sustainability




Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)







Take-back

Transparency


RoHS/REACH

Resource performance




Take-Back Program Available


Well-being performance



Lead Free



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant with Exemptions

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)