

Product datasheet

Specifications



APC Replacement Battery Cartridge #117 with 2 Year Warranty



APCRBC117

Overview

Lead time Usually in Stock

Main

Product or component type Replacement battery cartridge

Battery type Lead-acid battery

Provided equipment All required connectors
Battery recycling guide
Installation guide
Reusable packaging

Physical

Height 7.6 cm

Width 20.3 cm

Depth 58.4 cm

Net weight 22.27 kg

Mounting mode Not rack-mountable

Environmental

Ambient air temperature for operation 0...40 °C

Operating altitude 0...10000 ft

Relative humidity 0...95 %

Ambient air temperature for storage -15...45 °C

Storage altitude 0.00...15240.00 m

Storage Relative Humidity 0...95 %

Batteries & Runtime

Number of battery blocks per string 10

Number of battery free slots 0

Number of battery filled slots 0

Device mounting Enclosed battery cartridge

Battery voltage	120 V
Number of battery replacement quantity	1
Replacement battery	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	22.8 cm
Package 1 Width	39.3 cm
Package 1 Length	76.1 cm
Package 1 Weight	25.18 kg
SCC14	731304282679

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)