Product datasheet





APC Replacement Battery Cartridge 117 with 2 Year Warranty

APCRBC117

Overview

Lead Time Usually in Stock

Main

Product Or Component Type	Replacement battery cartridge
Battery Type	Lead-acid battery
Provided Equipment	All required connectors Battery recycling guide Installation guide Reusable packaging

Batteries & Runtime

Number Of Battery Blocks Per String	10
Number Of Battery Free Slots	0
Number Of Battery Filled Slots	0
Device Mounting	Enclosed battery cartridge
Battery Voltage	120 V
Number Of Battery Replacement Quantity	1

Physical

Height	7.6 cm
Width	20.3 cm
Depth	58.4 cm
Net Weight	22.27 kg
Mounting Mode	Not rack-mountable

Environmental

Operation Operator	040 °C
Operating Altitude	010000 ft
Relative Humidity	095 %
Ambient Air Temperature For Storage	-1545 °C
Storage Altitude	0.0015240.00 m
Storage Relative Humidity	095 %

Life Is On 26 Apr 2024

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	22.8 cm
Package 1 Width	39.3 cm
Package 1 Length	76.1 cm
Package 1 Weight	25.18 kg
Scc14	731304282679

Contractual warranty

Warranty 2 years repair or replace



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

Resource performance



Take-Back Program Available

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information