

# Product datasheet

Specifications



## APC Replacement battery cartridge #150 with 2 Year Warranty

APCRBC150

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage	12 V DC
Number of cables	1
Battery type	Lead-acid battery
Provided equipment	All required connectors Battery recycling guide Metallic battery tray or enclosure Reusable packaging Installation guide

### Physical

Colour	Black
Height	8.3 cm
Width	21.6 cm
Depth	34.3 cm
Net weight	10 kg
Mounting mode	Not rack-mountable
USB compatible	No

### Environmental

Ambient air temperature for operation	0...45 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m
Storage Relative Humidity	0...95 %

### Batteries & Runtime

Number of battery free slots 0

Number of battery filled slots	0
Device mounting	Enclosed battery cartridge
Number of battery replacement quantity	1

## Packing Units

Package 1 Weight	10.91 kg
Package 1 Height	15.2 cm
Package 1 width	36.8 cm
Package 1 Length	49.5 cm
Number of Units in Package 3	20

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------