

Product datasheet

Specifications



APC NetShelter 6U Low-Profile Wallmount Rack Enclosure Cabinet 230V Server Depth

AR106VI

Overview

Presentation	APC By Schneider Electric 6U Wall Mount is an innovative new way to deploy server and networking equipment at the Edge. The unique low-profile design enables large depth devices to be wall mounted in a compact and less intrusive form factor than traditional wall mount cabinets. It can ship pre-integrated with APC Smart UPS battery backup, NetBotz Physical and Environmental Security, and EcoStruxure IT, our cloud-based remote monitoring platform to stay connected at the Edge!
Lead Time	Usually Ships within 2 Weeks

Main

Product Or Component Type	Rack enclosure
Main Input Voltage	230 V
Input Connection Type	IEC 60320 C13
Number Of Rack Unit	6U

Physical

Height	64.8 cm
Width	35.3 cm
Depth	96.8 cm
Net Weight	36.29 kg
Colour	Black
Mounting Support	Wall
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Mounting Position	Vertical
Maximum Mounting Depth	76.2 cm
Minimum Mounting Depth	76.2 cm
Rack Width	19"
Permanent Permissible Load	113.40 kg dynamic 113.40 kg static

Input

Network Frequency	50 Hz
-------------------	-------

Conformance

Standards	UL 2416
-----------	---------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental

Air Flow	103.83 l/s
----------	------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	42.7 cm
Package 1 Width	73.4 cm
Package 1 Length	106.4 cm
Package 1 Weight	44.91 kg

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Sustainability




Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)




Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

 Energy Efficient Product

 Take-Back Program Available

Well-being performance

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile