

# Product datasheet

Specifications



## Network Power supply with battery backup, 12Vdc, 1A, BS1363, lithium battery

CP12010LI-UK

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage 220 V

Main Output Voltage 12 V DC

Rated power in W 12 W

Rated power in VA 12 VA

Battery type Li-Ion (Lithium-Ion)

### Physical

Height 7.8 cm

Width 4.8 cm

Depth 7.6 cm

Net weight 0.2 kg

Mounting preference No preference

Mounting mode Not rack-mountable

Two post mountable 0

USB compatible No

### Output

Maximum configurable power in W 12 W

### Conformance

Standards EN 55024  
EN 60950

### Environmental

Ambient air temperature for operation 0...40 °C

Relative humidity 5...95 %

---

Ambient air temperature for storage	-15...60 °C
-------------------------------------	-------------

## Batteries & Runtime

---

Number of battery filled slots	0
--------------------------------	---

---

Number of battery free slots	0
------------------------------	---

## Packing Units

---

Unit Type of Package 1	PCE
------------------------	-----

---

Number of Units in Package 1	1
------------------------------	---

---

Package 1 Height	11.3 cm
------------------	---------

---

Package 1 Width	9.9 cm
-----------------	--------

---

Package 1 Length	5.2 cm
------------------	--------

---

Package 1 Weight	0.28 kg
------------------	---------

---

SCC14	10731304344107
-------	----------------

## Offer Sustainability

---

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

## Contractual warranty

---

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)