

Product datasheet

Specifications



Easy UPS 3M Classic Battery Cabinet with batteries, IEC, 2 x 1000mm wide - Config D

E3MCBC10D

Overview

Presentation	Battery cabinet that includes batteries and battery breaker.
Lead time	Usually Ships within 6 Weeks

Main

Battery type	VRLA
Provided equipment	Installation guide

Physical

Height	189.5 cm
Width	200.4 cm
Depth	84.5 cm
Net weight	2182 kg
Mounting mode	Not rack-mountable

Environmental

Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...40 °C

Batteries & Runtime

Number of battery free slots	0
Number of battery filled slots	0
Device mounting	Enclosed battery cabinet

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	198 cm
Package 1 Width	97 cm
Package 1 Length	226 cm

Package 1 Weight 2222 kg

Offer Sustainability

REACH Regulation [REACH Declaration](#)

EU RoHS Directive Compliant
[EU RoHS Declaration](#)

Mercury free Yes

China RoHS Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

RoHS exemption information [Yes](#)

Recommended replacement(s)