

# Product datasheet

Specifications



## Classic Battery Cabinet, IEC, 700mm wide, Config D, Galaxy VS/ VL

GVSCBC7D

### Overview

<b>Presentation</b>	Battery cabinet that includes batteries and battery breaker.
<b>Lead time</b>	Special Order - Call for Quoted Lead Times

### Main

<b>Battery type</b>	VRLA
<b>Provided equipment</b>	Installation guide

### Physical

<b>Colour</b>	White
<b>Height</b>	190 cm
<b>Width</b>	71 cm
<b>Depth</b>	84.5 cm
<b>Net weight</b>	569 kg

### Environmental

<b>Ambient air temperature for operation</b>	0...40 °C
<b>Relative humidity</b>	0...95 % non-condensing
<b>Ambient air temperature for storage</b>	-15...40 °C

### Batteries & Runtime

<b>Number of battery free slots</b>	0
<b>Number of battery filled slots</b>	40
<b>Device mounting</b>	Enclosed battery cabinet

### Offer Sustainability

<b>EU RoHS Directive</b>	Under investigation
--------------------------	---------------------

### Recommended replacement(s)