

Product datasheet

Specifications

NetBotz Rack Monitor 250

NBRK0250



Overview

Lead time Usually in Stock

Main

Number of rack unit 1U

Number of cables 1

Communication port protocol HTTP
HTTPS
SNMP

Provided equipment Country-specific detachable power cord
Installation guide
Rack mounting brackets
Temperature/humidity sensor

Product compatibility Rack sensor pod 150

General

Connections supported Alarm beacon 1
Modbus Output (RS-485) 1
Relay output 1

Universal sensor supported Door contact
Dry contact
Humidity
Smoke
Fluid spot leak
Temperature
Vibration

Number of universal sensor ports 6

Number of sensor pods supported 0

Number of universal sensors supported 6

Sensor humidity 11...89 % +/- 3 % RH

Number of supported camera 0 integrated
0 networked
0 USB

Measurement range 15...50 °C +/- 1 °C
32...122 °F +/- 1.8 °F

Physical

Height 4.4 cm

Width	43.2 cm
Depth	5.9 cm
Net weight	1.27 kg
Mounting location	Front Rear
Mounting preference	No preference
Mounting mode	Not rack-mountable
Mounting position	Vertical

Environmental

Ambient air temperature for operation	0...45 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...65 °C
Storage altitude	0.00...15240.00 m
Storage Relative Humidity	0...95 %

Communications & Management

Communication network type	RJ45 10/100 Base-T
-----------------------------------	--------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.6 cm
Package 1 Width	22.6 cm
Package 1 Length	45.7 cm
Package 1 Weight	2.95 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
--------------------------	---

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------

Recommended replacement(s)