

# Product datasheet

Specifications

## NetBotz Rack Monitor 750

NBRK0750



### Overview

<b>Presentation</b>	The NetBotz Rack Monitor 750 provides integrated surveillance, sensing, access control, and advanced alerting for IT environments of all sizes, from single-rack edge networks to large data centers.
<b>Lead time</b>	Usually in Stock

### Main

<b>Number of rack unit</b>	1U
<b>Communication port protocol</b>	A-Link DHCP HTTPS IPv4 SNMP v1 SNMP v3 SSH v2 TCP/IP
<b>Provided equipment</b>	Rack mounting brackets Temperature/humidity sensor USB cable
<b>Product compatibility</b>	Rack sensor pod 150 Room sensor pod 155

### General

<b>Camera frame rate</b>	Up to 30 fps
<b>Display resolution</b>	Up to 1280x1024
<b>Universal sensor supported</b>	0-5V Door contact Dry contact Humidity Smoke Fluid spot leak Temperature Vibration
<b>Number of universal sensor ports</b>	6
<b>Number of sensor pods supported</b>	12
<b>Number of universal sensors supported</b>	78
<b>Number of supported camera</b>	4

### Physical

<b>Colour</b>	Black
---------------	-------

<b>Height</b>	4.3 cm
<b>Width</b>	43.2 cm
<b>Depth</b>	17.8 cm
<b>Net weight</b>	2.45 kg
<b>Mounting location</b>	Front Rear
<b>Mounting preference</b>	No preference
<b>Mounting mode</b>	Rack-mounted
<b>Mounting position</b>	Horizontal

## Conformance

<b>Standards</b>	CSA C22.2 No. 60950-1-03 FCC part 15 class A ICES-003 UL 60950-1
<b>Product certifications</b>	2014/30/EU AS/NZS 3548 (C-Tick) class A CE EMC directive 2004/108/EC VCCI class A

## Environmental

<b>Ambient air temperature for operation</b>	0...40 °C
<b>Operating altitude</b>	0...10000 ft
<b>Relative humidity</b>	0...95 %
<b>Ambient air temperature for storage</b>	-15...65 °C
<b>Storage altitude</b>	0.00...15240.00 m
<b>Storage Relative Humidity</b>	0...95 %

## Communications & Management

<b>Communication network type</b>	RJ45 10/100/1000 Base-T
-----------------------------------	-------------------------

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	12.1 cm
<b>Package 1 Width</b>	31.8 cm
<b>Package 1 Length</b>	53.3 cm
<b>Package 1 Weight</b>	4.17 kg

## Offer Sustainability

<b>EU RoHS Directive</b>	Under investigation
--------------------------	---------------------

## Recommended replacement(s)