Product datasheet

Specification





Power Cord Kit (6 ea), Locking, C19 to C20 (90 Degree), 1.8m

Free up space and secure power cords between rack-mount PDUs and attached IT

AP8716R

Overview

Presentation

| | equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads. |
|-----------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Lead Time | Usually in Stock |
| Main | |
| Input Connection Type | IEC 60320 C20 |
| Cable Length | 1.83 m |
| Number Of Cables | 6 |
| Provided Equipment | 3 left-angle jumper cords 3 right-angle jumper cords |
| Physical | |
| Colour | Black |
| Height | 30 cm |
| Width | 8 cm |
| Depth | 7 cm |
| Net Weight | 2.16 kg |
| Mounting Preference | No preference |
| Mounting Mode | Not rack-mountable |
| Input | |
| Max Line Current | 16 A |
| Input Current Limits | 16 A |
| Output | |

Conformance

Number Of Power Socket Outlets

Max Current Draw

Power Cable Length

16 A

1.83 m

1 IEC 60320 C19

| Product Certifications | CCC | |
|------------------------|-----------|--|
| | CSA | |
| | PSE | |
| | UL listed | |
| | VDE | |

Environmental

| Ambient Air Temperature For Operation | 075 °C |
|---------------------------------------|----------------|
| Relative Humidity | 2080 % |
| Operating Altitude | 010000 ft |
| Ambient Air Temperature For Storage | -2575 °C |
| Storage Relative Humidity | 2080 % |
| Storage Altitude | 0.0015240.00 m |

Packing Units

| • | |
|------------------------------|----------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 30 cm |
| Package 1 Width | 8 cm |
| Package 1 Length | 7 cm |
| Package 1 Weight | 2.16 kg |
| Scc14 | 10731304279713 |

Contractual warranty

Warranty 2 years repair or replace



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

Resource performance



Take-Back Program Available

Well-being performance



Lead Free

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |