

Product datasheet

Specifications



Toshiba Satellite 1600 series Notebook Battery

LBCTS6I

⚠ Discontinued on: 10 Jun 2022

⚠ Discontinued

Overview

Lead Time Usually in Stock

Main

Number Of Cables 1.0

Battery Type Ni-MH (Nickel-Metal Hydride)

Batteries & Runtime

Number Of Battery Free Slots 0

Number Of Battery Filled Slots 0

Battery Voltage 10.8 V

Battery Power In Vah 41 VAh

Physical

Height 21.59 cm

Width 13.97 cm

Depth 5.08 cm

Net Weight 0.68 kg

Mounting Mode Not rack-mountable

Output

Battery Capacity 3800 mA.h

Conformance

Product Certifications CE

Environmental

Ambient Air Temperature For Operation 10...40 °C

Operating Altitude 0...50000 ft

Relative Humidity 0...95 %

Ambient Air Temperature For Storage 0...55 °C

Storage Altitude 0.00...15240.00 m

Storage Relative Humidity 0...95 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 22.86 cm |
| Package 1 Width | 15.24 cm |
| Package 1 Length | 6.35 cm |
| Package 1 Weight | 0.908 kg |

Contractual warranty

| | |
|----------|--------------------------------|
| Warranty | 2 year (manufacturer's defect) |
|----------|--------------------------------|