

Product datasheet

Specifications



APC Service Bypass Panel, 230V, 125A, 2x hardwire input connectors, 8x IEC 60320 C19 outlets

SBP20KRM14U

Overview

Lead time Usually in Stock

Main

Main Input Voltage 220 V
230 V
240 V
380 V 3 phases
400 V 3 phases
415 V 3 phases

Main Output Voltage 230 V

Other Output Voltage 220 V
240 V

Number of rack unit 4U

Number of cables 1

Provided equipment Installation guide
Rack mounting brackets
User manual

Physical

Colour Black

Height 17.8 cm

Width 43.2 cm

Depth 57.2 cm

Net weight 18.78 kg

Mounting location Front

Mounting preference Lower

Mounting mode Rack-mounted

Input

Network frequency 50/60 Hz

Number of input connectors 1 hard wire 3-wire (1P + N + E)
1 hard wire 5 wire (3P + N + E)

Max line current 125 A

Input current limits 125 A

Load capacity 20000 VA

Power factor	0...1
--------------	-------

Output

Max current draw	125 A
Number of power socket outlets	8 IEC 60320 C19
Protection type	Circuit breaker
Efficiency	99 %

Conformance

Product certifications	CSA GOST
------------------------	-------------

Environmental

Ambient air temperature for operation	-20...50 °C
Relative humidity	0...95 %
Operating altitude	0...15000 ft
Ambient air temperature for storage	-40...65 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m

Packing Units

Package 1 Weight	31.36 kg
Package 1 Height	30.5 cm
Package 1 width	61 cm
Package 1 Length	84.3 cm
Number of Units in Package 3	6

Offer Sustainability

EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years (parts only)
----------	----------------------