

Product data sheet

Specifications



Rack PDU, Metered, Zero U, 11kW, 230V, (36) C13 & (6) C19

AP7857

⚠ Discontinued on: 14/06/2022

⚠ Discontinued

Overview

Lead Time While Supplies Last

Main

Colour	Black
Pdu Type	Metered
Cable Length	0.91 m
Provided Equipment	Installation guide Rack mounting brackets Toolless mounting kit User manual

Complementary

Main Input Voltage	400 V 3 phases
Height	177.8 cm
Width	5.6 cm
Main Output Voltage	230 V
Depth	4.4 cm
Net Weight	5.45 kg
Mounting Preference	No preference
Input Connection Type	IEC 60309 16 A 3P + N + PE
Mounting Mode	Rack-mounted
Input Current Limits	16 A
Network Frequency	50/60 Hz
Number Of Power Socket Outlets	36 IEC 60320 C13 6 IEC 60320 C19

Environment

Product Certifications	C-Tick CE GOST MIC Queensland Australia VDE
Ambient Air Temperature For Operation	-5...45 °C
Relative Humidity	5...95 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage Altitude	0.00...15240.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	213.4 cm
Package 1 Width	15.2 cm
Package 1 Length	12.7 cm
Package 1 Weight	8.841 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------