

Product data sheet

Specifications



UPS Communications Cable Smart Signalling

940-0024

Overview

Lead time Usually in Stock

Main

Cable length 2.00 m

Number of cables 1

Product compatibility UPS

Physical

Colour Black

Net weight 0.46 kg

Mounting location Front

Mounting mode Not rack-mountable

Cable end 2 SUB-D 9 male smart signaling

Cable end 1 SUB-D 9 female smart signaling

Output

Number of port 1

Environmental

Storage Relative Humidity 0...95 %

Storage altitude 0.00...15240.00 m

Ambient air temperature for operation 0...45 °C

Relative humidity 0...95 %

Operating altitude 0...10000 ft

Ambient air temperature for storage -15...45 °C

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1 1

Package 1 Height	22.9 cm
Package 1 Width	5.1 cm
Package 1 Length	10.2 cm
Package 1 Weight	0.46 kg

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
-------------------	--

WEEE The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty 2 years repair or replace

Recommended replacement(s)