

Product data sheet

Specifications



CDU Flexible Fluid Piping - 300 Feet (91.4 Meters)

ACAC20002

Overview

Lead time Usually Ships within 4 Weeks

General

Provided equipment Installation guide

Maximum recommended flowrate 1.17 l/s

Tube material PEX-AL-PEX

Pressure rating 1034.21 kPa

Fluid connection type Unterminated

Minimum bending radius 203.20 mm

Minimum fluid temperature 6 °C

Maximum fluid temperature 16 °C

Pressure drop per foot 1.28 kPa @ 0.88 l/s

Physical

Length 91.44 m

Colour White

Depth 106.7 cm

Height 27.9 cm

Net weight 37.73 kg

Width 106.7 cm

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1 1

Package 1 Height 31.8 cm

Package 1 Width 115.6 cm

Package 1 Length 115.6 cm

Package 1 Weight 39.55 kg

Number of Units in Package 3 6

Offer Sustainability

EU RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)
[EU RoHS Declaration](#)

Contractual warranty

Warranty

1 year (parts only)

Recommended replacement(s)