

Product data sheet

Specifications



CDU Flexible Fluid Piping - 300 Feet (91.4 Meters)

ACAC20002

Overview

Lead Time	Usually Ships within 4 Weeks
-----------	------------------------------

General

Provided Equipment	Installation guide
Maximum Recommended Flowrate	1.17 l/s
Tube Material	PEX-AL-PEX
Pressure Rating	1034.21 kPa
Fluid Connection Type	Unterminated
Minimum Bending Radius	203.20 mm
Minimum Fluid Temperature	6 °C
Maximum Fluid Temperature	16 °C
Pressure Drop Per Foot	1.28 kPa @ 0.88 l/s

Physical

Length	91.44 m
Colour	White
Depth	106.7 cm
Height	27.9 cm
Net Weight	37.73 kg
Width	106.7 cm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	31.8 cm
Package 1 Width	115.6 cm
Package 1 Length	115.6 cm
Package 1 Weight	39.55 kg
Number Of Units In Package 3	6

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
-------------------	--
