

Product data sheet

Specifications



RACK ATS, 120V, 20A, L5-20 IN, (10) 5-20R OUT



AP4452

! Discontinued on: 30 December 2022

! To be discontinued

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Input Connection Type	NEMA L5-20P
Number of rack unit	1U
Cable length	2.44 m
Number of cables	2
Provided equipment	Mounting hardware Rack mounting brackets Serial configuration cable

Physical

Colour	Black
Height	4.4 cm
Width	43.2 cm
Depth	23.6 cm
Net weight	4.4 kg
Mounting location	Front Rear
Mounting preference	No preference
Mounting mode	Rack-mounted

Input

Network frequency	50/60 Hz
[In] rated current	16 A
Max line current	20 A
Input current limits	20 A
Load capacity	1920 VA

Output

Max current draw	20 A
Number of power socket outlets	10 NEMA 5-20R
Protection type	Without circuit breaker

Conformance

Standards	EN 55022 class A FCC part 15 class A
-----------	---

Environmental

Ambient air temperature for operation	-5...45 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...15240.00 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.4 cm
Package 1 Width	35.6 cm
Package 1 Length	60 cm
Package 1 Weight	6.17 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)