

# Product data sheet

Specifications



## Rack PDU, Metered, 1U, 12A/208V, 10A/230V, (8) C13



AP7820B

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage	200 V 208 V 230 V
Main Output Voltage	208 V 230 V
Input Connection Type	IEC 60320 C14
Number of rack unit	1U
Cable length	1.98 m
Provided equipment	Cord retention bracket(s) Installation guide Rack mounting brackets User manual

### Physical

Height	4.4 cm
Width	44.4 cm
Depth	10.2 cm
Net weight	1.73 kg
Mounting location	Front Rear
Mounting preference	No preference
Mounting mode	Rack-mounted

### Input

[In] rated current	10 A
Input current limits	15 A
Load capacity	2300 VA
Network frequency	50/60 Hz

### Output

Rated current	10 A - 230 V 12 A - 208 V
---------------	------------------------------

Number of power socket outlets 8 IEC 60320 C13

## Conformance

Product certifications	cUL listed C-Tick CE CSA GOST UL listed VDE VCCI
Standards	FCC part 15 class A UL 60950

## Environmental

Ambient air temperature for operation	-5...45 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...15240.00 m

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.4 cm
Package 1 Width	33.7 cm
Package 1 Length	47 cm
Package 1 Weight	2.91 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

## Recommended replacement(s)