

Product data sheet

Specifications



Rack PDU, Metered, 1U, 16A, 208/230V, (8) C13



AP7821B

Overview

Lead time Usually in Stock

Main

Main Input Voltage	200 V 208 V 230 V
Main Output Voltage	208 V 230 V
Input Connection Type	IEC 60320 C20
Number of rack unit	1U
Cable length	2.50 m
Provided equipment	Cord retention bracket(s) Installation guide Rack mounting brackets User manual

Physical

Height	4.4 cm
Width	44.4 cm
Depth	10.2 cm
Net weight	1.74 kg
Mounting location	Front Rear
Mounting preference	No preference
Mounting mode	Rack-mounted

Input

[In] rated current	16 A
Input current limits	20 A
Load capacity	3300 VA
Network frequency	50/60 Hz

Output

Number of power socket outlets 8 IEC 60320 C13

Conformance

Product certifications	cUL listed C-Tick CE CSA GOST UL listed VCCI VDE
Standards	FCC part 15 class A ICES-003 UL 60950

Environmental

Ambient air temperature for operation	-5...45 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...15240.00 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.4 cm
Package 1 Width	33.7 cm
Package 1 Length	47 cm
Package 1 Weight	2.92 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)