Product data sheet

Specifications





Power Cord Kit (6 ea), Locking, C13 to C14, 1.8m, Blue

AP8706S-WWX591

Overview

Lead Time	Usually in Stock
Main	
Input Connection Type	IEC 60320 C14
Cable Length	1.83 m
Physical	
Colour	Blue
Height	24 cm
Width	7.5 cm
Depth	5.5 cm
Net Weight	1.35 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Input	
Max Line Current	10 A
Input Current Limits	10 A
Output	
Max Current Draw	10 A
Number Of Power Socket Outlets	1 IEC 60320 C13
Power Cable Length	1.83 m

Conformance

Product Certifications	CCC		
	PSE		
	VDE		
	VDE		

Environmental

Ambient Air Temperature For Operation	070 °C
Relative Humidity	2080 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2575 °C



Storage Relative Humidity	2080 %
Storage Altitude	0.0015240.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24 cm
Package 1 Width	5.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	1.35 kg

Contractual warranty

Warranty

2 years repair or replace

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.





Take-back Transparency RoHS/REACh

Resource performance

Take-Back Program Available

Well-being performance

Lead Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information



