

# Product data sheet

Specifications



## Power Cord Kit (6 EA), Locking, C19 TO C20, 0.6M (2FT), Red

AP8712SX340

### Overview

Lead time Usually in Stock

### Main

Input Connection Type IEC 60320 C20

Cable length 0.61 m

Number of cables 6

### Physical

Colour Red

Height 30 cm

Width 6 cm

Depth 6.5 cm

Net weight 1.12 kg

Mounting preference No preference

Mounting mode Not rack-mountable

### Input

Max line current 16 A

Input current limits 16 A

### Output

Max current draw 16 A

Number of power socket outlets 1 IEC 60320 C19

Power cable length 0.61 m

### Conformance

Product certifications CCC  
CSA  
PSE  
UL listed  
VDE

## Environmental

Ambient air temperature for operation	0...75 °C
Relative humidity	20...80 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...75 °C
Storage Relative Humidity	20...80 %
Storage altitude	0.00...15240.00 m

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	30 cm
Package 1 Width	6.5 cm
Package 1 Length	6 cm
Package 1 Weight	1.12 kg
Number of Units in Package 3	390

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

## Recommended replacement(s)