

# Product data sheet

Specifications



## Power Cord Kit (6 ea), Locking, C19 to C20 (90 Degree), 1.2m

AP8714R

### Overview

**Presentation** Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.

**Lead time** Usually in Stock

### Main

**Input Connection Type** IEC 60320 C20

**Cable length** 1.22 m

**Number of cables** 6

**Provided equipment** 3 left-angle jumper cords  
3 right-angle jumper cords

### Physical

**Colour** Black

**Height** 30 cm

**Width** 6.5 cm

**Depth** 7 cm

**Net weight** 1.64 kg

**Mounting preference** No preference

**Mounting mode** Not rack-mountable

### Input

**Max line current** 16 A

**Input current limits** 16 A

### Output

**Max current draw** 16 A

**Number of power socket outlets** 1 IEC 60320 C19

**Power cable length** 1.22 m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Conformance

Product certifications	CCC CSA PSE UL listed VDE
------------------------	---------------------------------------

## Environmental

Ambient air temperature for operation	0...75 °C
Relative humidity	20...80 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...75 °C
Storage Relative Humidity	20...80 %
Storage altitude	0.00...15240.00 m

## Packing Units

Package 1 Height	30 cm
Package 1 Width	6.5 cm
Package 1 Length	7 cm
Package 1 Weight	1.64 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	9
Package 2 Height	143.99 cm
Package 2 Width	100 cm
Package 2 Length	120 cm
Package 2 Weight	14.733 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	9
Package 3 Height	25 cm
Package 3 Width	33.5 cm
Package 3 Length	56.5 cm
Package 3 Weight	14.733 kg
SCC14	10731304279690

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Lead free	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

**Recommended replacement(s)**