

Product data sheet

Specifications



Power Cord Kit (6 EA), Locking, C19 TO C20, 1.2M (4FT), Red

AP8714SX340

Overview

Lead time Usually in Stock

Main

Input Connection Type IEC 60320 C20

Cable length 1.22 m

Number of cables 6

Physical

Colour Red

Height 30 cm

Width 7 cm

Depth 7 cm

Net weight 1.64 kg

Mounting preference No preference

Mounting mode Not rack-mountable

Input

Max line current 16 A

Input current limits 16 A

Output

Max current draw 16 A

Number of power socket outlets 1 IEC 60320 C19

Power cable length 1.22 m

Conformance

Product certifications CCC
CSA
PSE
UL listed
VDE

Environmental

Ambient air temperature for operation	0...75 °C
Relative humidity	20...80 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...75 °C
Storage Relative Humidity	20...80 %
Storage altitude	0.00...15240.00 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	30 cm
Package 1 Width	7 cm
Package 1 Length	7 cm
Package 1 Weight	1.64 kg
Number of Units in Package 3	270

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)