

Product data sheet

Specifications



Extension Cable for use w/ UPS communications cable 15'/5m

AP9815

Overview

Lead time Usually in Stock

Main

Cable length 4.57 m

Number of cables 1

Product compatibility UPS

Physical

Colour Grey

Net weight 0.45 kg

Mounting location Front

Mounting mode Not rack-mountable

Cable end 2 SUB-D 9 male Serial Straight Through

Cable end 1 SUB-D 9 female Serial Straight Through

Environmental

Storage Relative Humidity 0...95 %

Storage altitude 0.00...15240.00 m

Ambient air temperature for operation 0...45 °C

Relative humidity 0...95 %

Operating altitude 0...10000 ft

Ambient air temperature for storage -15...45 °C

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1 1

Package 1 Height 22.9 cm

Package 1 Width 5.1 cm

Package 1 Length 10.2 cm

Package 1 Weight	0.45 kg
-------------------------	---------

Offer Sustainability

Sustainable offer status	Green Premium product
---------------------------------	-----------------------

REACH Regulation	REACH Declaration
-------------------------	-----------------------------------

EU RoHS Directive	Compliant EU RoHS Declaration
--------------------------	--

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
-------------	---

Optimized Energy Efficiency	Energy efficient product
------------------------------------	--------------------------

Take-back	Take-back program available
------------------	-----------------------------

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------

Recommended replacement(s)