

Product data sheet

Specifications



UPS Signaling Offer for IBM AS/400 and IBMi (IBM Power Systems)

AP98275

Overview

Lead time Usually in Stock

Physical

Height 3.8 cm

Width 17.8 cm

Depth 15.2 cm

Net weight 0.36 kg

Mounting mode Not rack-mountable

Cable end 2 SUB-D 9 male simple signaling

Cable end 1 SUB-D 9 male simple signaling

Output

Number of port 1

Environmental

Storage Relative Humidity 0...95 %

Storage altitude 0.00...15240.00 m

Ambient air temperature for operation 0...45 °C

Relative humidity 0...95 %

Operating altitude 0...50000 ft

Ambient air temperature for storage -15...45 °C

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1 1

Package 1 Height 5.1 cm

Package 1 Width 16.5 cm

Package 1 Length 23.5 cm

Package 1 Weight 0.45 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------

Recommended replacement(s)