

Product data sheet

Specifications



UPS Signaling Offer for IBM AS/400 and IBMi (IBM Power Systems)

AP98275

Overview

Lead Time	Usually in Stock
-----------	------------------

Physical

Height	3.8 cm
Width	17.8 cm
Depth	15.2 cm
Net Weight	0.36 kg
Mounting Mode	Not rack-mountable
Cable End 2	SUB-D 9 male simple signaling
Cable End 1	SUB-D 9 male simple signaling

Output

Number Of Port	1
----------------	---

Environmental

Storage Relative Humidity	0...95 %
Storage Altitude	0.00...15240.00 m
Ambient Air Temperature For Operation	0...45 °C
Relative Humidity	0...95 %
Operating Altitude	0...50000 ft
Ambient Air Temperature For Storage	-15...45 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.1 cm
Package 1 Width	16.5 cm
Package 1 Length	23.5 cm
Package 1 Weight	0.45 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability




Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)




Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

 Energy Efficient Product

 Take-Back Program Available

Well-being performance

 Lead Free

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins