Product data sheet

Specifications



Power Cord, C13 to C20, 2.0m

AP9879



Overview

Lead Time	Usually in Stock
Main	
Input Connection Type	IEC 60320 C20
Cable Length	1.98 m
Number Of Cables	1
Physical	
Colour	Black
Net Weight	0.36 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Input	
Max Line Current	10 A
Output	
Max Current Draw	10 A
Number Of Power Socket Outlets	1 IEC 60320 C13
Conformance	
Product Certifications	UL listed
Packing Units	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30.5 cm
Package 1 Width	10.2 cm
Package 1 Length	10.2 cm
Package 1 Weight	0.459 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10

Package 2 Height

23 cm



Package 2 Width	33 cm
Package 2 Length	52.5 cm
Package 2 Weight	5.5 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	10
Package 3 Height	143.99 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	5.5 kg

Contractual warranty

Warranty

2 years repair or replace

2

Sustainability

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.





Take-back Transparency RoHS/REACh

Resource performance

Take-Back Program Available

Well-being performance

Lead Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information



